

Dental Air Compressors



EUROCOMPRESS[®]
AIR COMPRESSORS

DENTAL DIVISION

Shark II



| Cod. | SHARK II OILLESS MODEL | Units | AIR Tank | dB (A) | air displacement lt/min cfm | F.A.D. lt/min cfm | HP KW | volt Hz | type | cyl. | R.P.M. | bar psi | cm. a x b x c | kg. Lbs |
|---------|------------------------|-------|----------|--------|-----------------------------|-------------------|---------|---------|---------|------|--------|---------|---------------|---------|
| 370.250 | 50/150V | 2 | 50 | 68 | 200 7 | 125 4,4 | 1,5 1,1 | 230/50 | EXTREME | 2v | 1400 | 8 114 | 64x39x77 | 40 88 |
| 385.100 | 50/150V DRY | 2 | 50 | 68 | 200 7 | 125 4,4 | 1,5 1,1 | 230/50 | EXTREME | 2v | 1400 | 8 114 | 64x49x77 | 45 99 |
| 370.251 | 50/200V | 2-3 | 50 | 75 | 200 7 | 150 5,3 | 2 1,5 | 230/50 | VS 204 | 2v | 1400 | 8 114 | 64x39x77 | 45 99 |
| 385.101 | 50/200V DRY | 2-3 | 50 | 75 | 200 7 | 150 5,3 | 2 1,5 | 230/50 | VS 204 | 2v | 1400 | 8 114 | 64x49x77 | 50 110 |
| 370.252 | 50/230V | 3 | 50 | 68 | 250 8,8 | 180 6,4 | 2 1,5 | 230/50 | EXTREME | 2v | 1400 | 8 114 | 64x39x77 | 42 92 |
| 385.102 | 50/230V DRY | 3 | 50 | 68 | 250 8,8 | 180 6,4 | 2 1,5 | 230/50 | EXTREME | 2v | 1400 | 8 114 | 64x49x77 | 47 103 |
| 370.253 | 50/250V | 3 | 50 | 75 | 250 8,8 | 190 6,8 | 2,5 1,8 | 230/50 | VS 254 | 2v | 1400 | 8 114 | 64x39x77 | 45 99 |
| 385.103 | 50/250V DRY | 3 | 50 | 75 | 250 8,8 | 190 6,8 | 2,5 1,8 | 230/50 | VS 254 | 2v | 1400 | 8 114 | 64x49x77 | 50 110 |

By request: Volt 230/60 Hz - Volt 115/60 Hz



Shark II Silent



| Cod. | SHARK II SILENT MODEL | Units | AIR Tank | dB (A) | air displacement lt/min cfm | F.A.D. lt/min cfm | HP KW | volt Hz | type | cyl. | R.P.M. | bar psi | cm. a x b x c | kg. Lbs |
|---------|-----------------------|-------|----------|--------|-----------------------------|-------------------|---------|---------|---------|------|--------|---------|---------------|---------|
| 390.200 | 50/150V | 2 | 50 | 60 | 200 7 | 125 3,9 | 1,5 1,1 | 230/50 | EXTREME | 2v | 1400 | 8 114 | 64x40x92 | 46 101 |
| 395.050 | 50/150V DRY | 2 | 50 | 60 | 200 7 | 125 3,9 | 1,5 1,1 | 230/50 | EXTREME | 2v | 1400 | 8 114 | 64x50x92 | 51 112 |
| 390.201 | 50/200V | 2-3 | 50 | 64 | 200 7 | 150 5,3 | 2 1,5 | 230/50 | VS 204 | 2v | 1400 | 8 114 | 64x40x92 | 51 112 |
| 395.051 | 50/200V DRY | 2-3 | 50 | 64 | 200 7 | 150 5,3 | 2 1,5 | 230/50 | VS 204 | 2v | 1400 | 8 114 | 64x50x92 | 56 123 |
| 390.202 | 50/230V | 3 | 50 | 60 | 250 8,8 | 180 6,4 | 2 1,5 | 230/50 | EXTREME | 2v | 1400 | 8 114 | 64x40x92 | 48 105 |
| 395.052 | 50/230V DRY | 3 | 50 | 60 | 250 8,8 | 180 6,4 | 2 1,5 | 230/50 | EXTREME | 2v | 1400 | 8 114 | 64x50x92 | 53 116 |
| 390.203 | 50/250V | 3 | 50 | 64 | 250 8,8 | 190 6,8 | 2,5 1,8 | 230/50 | VS 254 | 2v | 1400 | 8 114 | 64x40x92 | 51 112 |
| 395.053 | 50/250V DRY | 3 | 50 | 64 | 250 8,8 | 190 6,8 | 2,5 1,8 | 230/50 | VS 254 | 2v | 1400 | 8 114 | 64x50x92 | 56 123 |

By request: Volt 230/60 Hz - Volt 115/60 Hz



20090 Trezzano sul Naviglio (MI) ITALY - Via Brunelleschi, 16/20
 Tel.: +39/02.44.54.656 - 02.44.50.027 - Fax: +39/02.44.50.027
 E-mail: eurocompress@eurocompress.it - http://www.eurocompress.it